

Ionpure® LX-HI Instant Hot Water Sanitizable Continuous Electrodeionization(CEDI) Modules

Ionpure® LX Module – LX-HI



Hot water sanitization has been shown to be more effective than chemical sanitization for controlling microbiological growth. Ease of operation, maximum reliability and low operating costs are signature features of Ionpure® modules. LX-HI modules are ideal for pharmaceutical, biotechnology and other applications where chemical-free, instant hot water sanitization is desired. LX-HI modules produce high purity water without regeneration downtime.



LX-HI Series Features

- Hot water sanitizable at 185°F/85°C ±5°C
- Continuous operation up to 140°F (60°C)
- US Patented technology for instant hot water capability – no ramp up/down required
- Higher sanitization pressures 30 psi/2.0 bar
- Double O-ring seal guarantees leak-free operation
- Proven performance after +150 sanitizations
- Concentrate recirculation and brine injection not required
- Wetted materials of construction comply with FDA requirements

For additional information call +31 165 348 253 or visit our website at www.purewatergroup.com



Ionpure® LX-HI Instant Hot Water Sanitizable Continuous Electrodeionization (CEDI) Modules

Operating environment

Installation should be indoors with no direct sunlight and it should have a maximum ambient temperature of 113°F (45°C).

Quality Assurance Standards

CE marked. Each module is factory tested to meet strict industry standards and is manufactured in an ISO 9001 and ISO 14000 quality and environmental management system.

Maximum Feed Water Specifications	
Feed water conductivity equivalent, Including CO ₂ and Silica	< 40 µS/cm
Feed water source	RO permeate
Temperature	40 - 140°F (5 - 60°C)
Inlet pressure	20 - 100 psi (1.4 - 7 bar)
Maximum total chlorine (as Cl ₂)	< 0.02 ppm
Iron (Fe)	< 0.01 ppm
Manganese (Mn)	< 0.01 ppm
Sulphide (S ⁻)	< 0.01 ppm
pH	4 - 11
Total hardness (as CaCO ₃)	< 1.0 ppm
Dissolved organics (TOC as C)	< 0.5 ppm
Silica (SiO ₂)	< 1.0 ppm

Item Number	Physical Specifications	
	Dimensions	
	L +/- 0.25"(6.4 mm)	C +/- 0.13" (3.2 mm)
LXM04HI-3	11.81" (300.0 mm)	7.47" (189.7 mm)
LXM10HI-3	15.29" (388.6 mm)	10.96" (278.5 mm)
LXM18HI-3	19.91" (505.7 mm)	15.62" (396.7 mm)
LXM24HI-3	23.38" (593.9 mm)	19.12" (485.6 mm)
LXM30HI-3	27.42" (696.5 mm)	22.61" (574.2 mm)
LXM45HI-3	35.72" (907.3 mm)	31.35" (796.3 mm)

Typical Module Performance

Operating Parameters	
Recovery	90 - 95%
Maximum Feed Pressure	100 psi (7 bar)
Pressure Drop Range at Nominal Flow	20 - 30 psi (1.4 - 2.1 bar)
Maximum Feed Temperature	140°F (60°C)
Sanitization Temperature at 30 psi (2.0 bar)	185°F (85°C)
DC voltage	0 - 600
DC amperage	0 - 10
Product Water Quality	
Product conductivity	< 0.1µS/cm*
Silica (SiO ₂) removal	90 - 99% depending on feed conditions

*Actual performance may be determined using the IP-Pro projection software available from Ionpure.

Model Number	Flow and Physical Specifications				
	Product Flow min. gpm (m ³ /h)	Product Flow nominal gpm (m ³ /h)	Product Flow max. gpm (m ³ /h)	Shipping Weight lbs (kg)	Operating weight lbs (kg)
IP-LXM04HI-3	1.0 (0.22)	2.0 (0.44)	3.0 (0.67)	150 (68)	110 (50)
IP-LXM10HI-3	2.5 (0.55)	5.0 (1.1)	7.5 (1.65)	200 (91)	150 (68)
IP-LXM18HI-3	4.5 (1.1)	9.0 (2.0)	13.5 (3.1)	220 (100)	170 (77)
IP-LXM24HI-3	6.3 (1.4)	12.5 (2.8)	18.8 (4.2)	250 (113)	200 (91)
IP-LXM30HI-3	7.5 (1.65)	15.0 (3.3)	22.5 (5.11)	270 (123)	220 (100)
IP-LXM45HI-3	11.3 (2.55)	22.5 (5.1)	33.8 (7.67)	320 (145)	270 (122.5)

Pure Water Group

Korte Hei 3
4714 RD Sprundel
Tel. +31 165 348 253
Fax +31 165 348 254
info@purewatergroup.com

Ionpure and Flexmount are trademarks of Evoqua, its subsidiaries or affiliates.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in terms and of the contract